

EpoPro 8770A/B

Semi-Rigid, Room Temperature Curing, Epoxy Encapsulating System

EpoPro® 8770A/B is a low viscosity, easy to use, room temperature curing encapsulation system which produces tough, glossy castings. This system is designed as an excellent general-purpose casting and impregnation system. It has excellent adhesion to FR-4, metals, and most plastics. The cured encapsulant is thermal shock and impact resistant and is resistant to moisture, solvents, and many chemicals include petroleum products and weak acids and bases. The cured polymer is resistant to heat aging and to cryogenic exposure to at least -40°C.

EpoPro 8770A/B has been used for both impregnating and casting electrical components. Its viscosity allows the user to impregnate coils or fill tightly spaced components without difficulty and makes it easier to achieve a bubble free casting. It is also can be used as a binder for silica flour, sand or other low cost fillers used in some electrical insulating applications.

Low cost filled variants are available as part of the EpoPro 271 series and modified versions of the EpoPro 8770 system are also available by request. Custom colors, faster or slower cure speeds and modified viscosities are all available. Please contact us to discuss your application if you think a modified version might be useful in your application.

TYPICAL APPLICATIONS

- General potting of electronic devices
- Encapsulation of stress-sensitive components
- Low-voltage encapsulation

HANDLING PROPERTIES

	<u>VALUE</u>	<u>TEST METHOD</u>
<u>EpoPro 8770A</u>		
Density, g/cm ³	1.15	ASTM E-201
Viscosity @ 25°C, cps	1900	ASTM D-2393
<u>EpoPro 8770B</u>		
Density, g/cm ³	1.00	ASTM E-201
Viscosity @ 25°C, cps	600	ASTM D-2393
Mix Ratio By Weight	100A:100B	Calculated
Mix Ratio By Volume	100A:100B	Calculated
Viscosity Mixed @ 25°C / @ 40°C, cps	1200 / 350	ASTM D-2393
Gel Time @ 25°C, 100g mass	35 minutes	ASTM D-2471
Recommended Cure Schedules:	24 hrs. @ 25°C or allow to gel (~45 min @ 25°C) then cure for 2 hrs @ 65°C or 1 hr @ 80°C	

PHYSICAL PROPERTIES

Product Datasheet



	<u>VALUE</u>		<u>TEST METHOD</u>
Color	Black	Visual	
Density, g/cm ³	1.08		ASTM E-201
Shore Hardness	70D		ASTM D-2240
Tensile Strength, psi	4500		ASTM D-638
Tensile Elongation at break	8%		ASTM D-638
Water Absorption, % by weight 7 days @ 25°C	0.30%		ASTM D-570
Glass Transition Temp. (Tg)	60°C		
Coefficient of Thermal Exp. (CTE)	60 ppm/°C		ASTM E -381
Curing Shrinkage	0.1%		ASTM D-792

ELECTRICAL PROPERTIES

	<u>VALUE</u>			<u>TEST METHOD</u>
Electrolytic Corrosion	Grade A-1			DIN 53489
Dielectric Strength, V/mil	>600			ASTM D-149
	<u>@23°C</u>	<u>@40°C</u>	<u>@80°C</u>	
Volume Resistivity, ohm-cm	2.1x10 ¹⁵	3x10 ¹⁴	1.5x10 ¹¹	ASTM D-257
Dielectric Constant, 60 Hz	4.1	4.1	5.8	ASTM D-150
Dielectric Constant, 1 MHz	3.0	-	-	ASTM D-150
Dissipation Factor, 60 Hz	0.008	0.008	0.04	ASTM D-150
Dissipation Factor, 1M Hz	0.01	-	-	ASTM D-150

NOTE : Typical Properties determined using EpoPro 8770A/B cured for for 48 hours @ 25°C. Values are based on laboratory or average production results – not for specification purposes.

SUGGESTED PROCESSING GUIDELINES:

EpoPro 8770A/B can be applied by pouring, brushing, roller, squeegee, knife, spatula, or by spraying or dipping. It suitable for meter-mix dispensing and can be supplied in premixed and frozen syringes for small volume applications.

Weigh resin and hardener in the recommended ratio as accurately as possible into a clean mixing container. Always use weighing equipment having accuracy in proportion to the amounts being weighted – ideally the accuracy of the scale should be less than 1% of the mass being weighed. Blend by using a spatula or stirring stick for 2-3 minutes using a kneading motion. Scrape the bottom and sides of the mixing container carefully and frequently to produce a uniform mixture.

For best adhesion apply to clean, dry surfaces. Allow to cure at room temperature for 24-48 hours or allow to set at 25°C for 3-4 hours then heat cure at 65°C cure for 4 hours. For small volume application immediate heat cures may be possible and more rapid cures may be possible at higher temperatures. If you would like recommendation on alternate cures please contact us. Always evaluate a suggested cure schedule in your application prior to implementing it for full scale production as each application unique conditions can effect the results.

STORAGE GUIDELINES:

Product Datasheet



Store this material in a clean, cool and dry environment in its tightly closed original container. Products may settle during storage and should be thoroughly re-mixed prior to use. Avoid extended exposure to high humidity. Tightly re-seal after use. If the recommended storage conditions are observed the products will have a minimum shelf-life of 12 months from the date of shipment.

HANDLING PRECAUTIONS:

Mandatory and recommended industrial hygiene procedures should be followed whenever these products are being handled and processed. For additional information please consult the corresponding material safety data sheets.

PERSONAL HYGIENE:

EpoPro 8770A

CAUTION! May cause eye irritation. Prolonged or repeated skin contact may cause irritation, may cause allergic skin reaction. Avoid contact with eyes, skin, or clothing. Wear eye protection and impervious gloves when handling. Wash thoroughly after handling. Avoid breathing vapor or mist. Keep containers closed when not in use. Use only with adequate ventilation. Do not take internally.

EpoPro 8770B

WARNING! May cause skin and eye irritation. May cause allergic skin and respiratory reactions. Harmful if inhaled or swallowed. Do NOT get in eyes, on skin, or clothing. Wear chemical splash goggles and impervious gloves when handling. Wash skin and clothing thoroughly after handling. Avoid breathing vapor or mist. Use only with adequate ventilation. Keep containers closed when not in use. Do NOT take internally.

FIRST AID

In case of contact:

Skin – Immediately wash skin thoroughly with mild soap and water. Remove contaminated clothing and wash before reuse. Destroy contaminated shoes and other articles made of leather.

Eyes – Immediately flush eyes with plenty of water for 15 minutes and get prompt medical attention.

Inhalation - Remove person to fresh air. Administer oxygen or artificial respiration if necessary. Call a physician.

Ingestion - Do not induce vomiting. Dilute with plenty of water and contact physician immediately. Never give anything by mouth to an unconscious person.

DISCLAIMER:

IMPORTANT: The following supercedes Buyer's documents. **SELLER / MANUFACTURER MAKES NO REPRESENTATION OR WARRANTY, EXPRESS OR IMPLIED, INCLUDING OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** No statements herein are to be construed as inducements to infringe any relevant patent. Under no circumstances shall Seller / Manufacturer be liable for incidental, consequential or indirect damages for alleged negligence, breach of warranty, strict liability, tort or contract arising in connection with the product(s). Buyer's sole remedy and Seller's sole liability for any claims shall be Buyer's purchase price. Data and results presented are based on controlled or laboratory work and must be confirmed by Buyer by testing for its intended conditions of use. The product(s) has not been tested for, and is therefore not recommended for, uses for which prolonged contact with mucous membranes, abraded skin, or blood is intended; or for uses for which implantation within the human body is intended.

Specialty Polymers & Services, Inc. (SP&S)
27822 Fremont Court
Valencia, CA 91355
www.spolymers.com

Tel - 661-294-1790
Fax - 661-294-0640
info@spolymers.com